

# jetOPTIMUS® Transfection Reagent

## DNA Transfection

### Day 0: Cell Seeding


- Seed cells in  $V$  mL of cell growth medium according to the table below

Culture vessel	Number of cells*	$V$ = volume of medium during transfection [mL]
96-well	7,500–25,000	0.125
24-well	40,000–100,000	0.5
12-well	80,000–200,000	1
6-well/35 mm	150,000–400,000	2
60 mm/flask 25 cm <sup>2</sup>	200,000–850,000	5
100 mm/flask 75 cm <sup>2</sup>	$1 \times 10^6$ – $4 \times 10^6$	10

Quantities per well, dish or flask.

### Day 1: Transfection Using jetOPTIMUS® Reagent

- Use jetOPTIMUS® buffer only
- Transfect cells at 60–80% confluence



Culture vessel	$W$ = volume of jetOPTIMUS® buffer [µL]	$X$ = amount of DNA added [µg]	$Y$ = volume of jetOPTIMUS® reagent [µL]
96-well	12.5	0.13	0.13–0.19
24-well	50	0.5	0.5–0.75
12-well	100	1	1–1.5
6-well/35 mm	200	2	2–3
60 mm/flask 25 cm <sup>2</sup>	500	4	4–6
100 mm/flask 75 cm <sup>2</sup>	1,000	10	10–15

Quantities per well, dish or flask.

### Day 2–3: Measure Gene Expression

See back page for optimization tips.

Download complete protocol on [sartorius.com](http://sartorius.com)

# Short Protocol – Optimization Tips

## Protocol Optimization

- Test different DNA amounts: X, 0.5X and 1.5X
- Test different DNA/jetOPTIMUS® ratios, 1:1 to 1:1.5.
- For cell specific protocols, visit our website at [www.sartorius.com](http://www.sartorius.com).

Culture vessel	W = volume of jetOPTIMUS® buffer [µL]	X = amount of DNA added [µg]	Y = volume of jetOPTIMUS® reagent [µL]
96-well	12.5	0.10–0.20	0.10–0.30
24-well	50	0.25–0.75	0.25–1
12-well	100	0.5–1.5	0.5–2.25
6-well/35 mm	200	1–3	1–4.5
60 mm/flask 25 cm <sup>2</sup>	500	2–6	2–9
100 mm/flask 75 cm <sup>2</sup>	1,000	5–15	5–22

Quantities per well, dish or flask.

## Tips to Increase Cell Viability of Sensitive Cells

- Replace medium 4 hours after transfection.
- Decrease DNA amount to 0.5X while maintaining the DNA/jetOPTIMUS® ratio previously used.
- Analyze transfection at an earlier time point (24 hours after transfection instead of 48 hours for instance).
- Perform transfection in reduced serum medium for sensitive cells.
- Check that the target gene does not affect cell viability.
- Ensure that cells have been passaged more than twice and less than 20 times prior to transfection.
- Discard overconfluent cells.

## Good DNA Transfection Practices

- Store appropriately jetOPTIMUS® (5±3 °C).
- Regularly check for mycoplasma contamination.
- Use a reporter gene to set up and optimize transfection conditions.
- Serum quality may drastically affect transfection efficiency. When purchasing a new batch of serum or trypsin, check cell viability as well as transfection efficiency.

## ⚠ NOTE:

Please refer to the complete protocol available on [www.sartorius.com](http://www.sartorius.com).

## Germany

Sartorius Lab Instruments  
GmbH & Co. KG  
Otto-Brenner-Strasse 20  
37079 Goettingen  
Phone +49 551 308 0

## USA

Sartorius Corporation  
565 Johnson Avenue  
Bohemia, NY 11716  
Phone +1 631 254 4249  
Toll-free +1 800 635 2906

🌐 For further information, visit  
[sartorius.com](http://sartorius.com)